



Product specification

**UV cuvette, 2 ml, (HxW): 45 x 12.5 mm, special plastic,
transparent, optical sides: 2**



Product information

Product number	67.759.001
----------------	------------

Product descriptions

Name	UV cuvette, 2 ml, (HxW): 45 x 12.5 mm, special plastic, transparent, optical sides: 2
Product number	67.759.001
Product description	UV cuvette, max. working volume: 2 ml, material: special plastic, transparent, (HxW): 45 x 12.5 mm, optical sides: 2, suitable for use beginning at 220 nm, path length: 10 mm, centre height: 15 mm, sorted by mould cavity number, free from DNA/RNase/protein, 100 piece(s)/polystyrene container

Material & colours

Color of product	transparent
Closure material	Low Density Polyethylene (LD-PE)
Color of cap	red

Size

Width of product	12.5 mm
Height of product	45 mm

Max. volume	2.5 ml
-------------	--------

Product characteristics

Path length	10 mm
Wavelength in the cuvette area	220 nm
Centre height	15 mm
Closure type	Push cap

Purity & certification

Product category	not regulated
CE certified	no CE mark
Purity standard	free from DNA/RNase/protein
Batched	yes

Packaging

Type of inner packaging	Box
Piece(s) / inner box	100
Piece(s) / case	400
Piece(s) / pallet	31200
Height of inner box	56 mm
Width of inner box	202 mm
Depth of inner box	222 mm
Height of case	130 mm
Width of case	278 mm
Depth of case	418 mm
Volume of case	0.0151 cbm
Weight of case	1.41 kg
EAN inner box	4038917264501
EAN case	4038917264495

This is the current specification for this product. Sarstedt reserves the right to make changes, in full or in part, at any time without prior notification.

This specification is confidential and the property of Sarstedt. It is neither to be duplicated nor made available to third parties without our prior written consent.



SARSTEDT

This document was prepared by EDP support and is valid without signature.