



## Product specification

### Rack, PC, format: 10 x 2, suitable for screw cap micro tubes



## Product information

|                |            |
|----------------|------------|
| Product number | 93.848.100 |
|----------------|------------|

## Product descriptions

|                     |  |
|---------------------|--|
| Name                | Rack, PC, format: 10 x 2, suitable for screw cap micro tubes   |
| Product number      | 93.848.100   |
| Product description | Rack, material: PC, transparent, format: 10 x 2, (LxWxH): 257 x 62 x 40 mm, for 20 collection tubes, suitable for screw cap micro tubes, 1 piece(s)/case |

## Material & colours

|                  |             |
|------------------|-------------|
| Color of product | transparent |
|------------------|-------------|

## Size

|                   |        |
|-------------------|--------|
| Width of product  | 62 mm  |
| Length of product | 257 mm |
| Height of product | 40 mm  |

## Product characteristics

|                  |            |
|------------------|------------|
| Label/Print      | With print |
| Storage capacity | 20         |

|                        |        |
|------------------------|--------|
| Autoclavable (max. °C) | 121 °C |
|------------------------|--------|

## Purity & certification

|                  |               |
|------------------|---------------|
| Product category | not regulated |
| CE certified     | no CE mark    |
| Batched          | no            |

## Packaging

|                     |               |
|---------------------|---------------|
| Piece(s) / case     | 60            |
| Piece(s) / pallet   | 1800          |
| Height of inner box | 260 mm        |
| Width of inner box  | 43 mm         |
| Depth of inner box  | 65 mm         |
| Height of case      | 340 mm        |
| Width of case       | 398 mm        |
| Depth of case       | 398 mm        |
| Volume of case      | 0.0539 cbm    |
| Weight of case      | 12.43 kg      |
| EAN inner box       | 4038917121736 |
| EAN case            | 4038917017985 |

This is the current specification for this product. Sarstedt reserves the right to make changes, in full or in part, at any time without prior notification.

This specification is confidential and the property of Sarstedt. It is neither to be duplicated nor made available to third parties without our prior written consent.

This document was prepared by EDP support and is valid without signature.



# SARSTEDT